Technical data sheet



DV270.2

Execution for: Marine CRUISE

Utensil washer

Working direction: left - right Working height: 850 mm 3-phase current 3 PE 460V 60Hz Fresh water line: Soft cold water 0-3 °GH Steam-heated boiler and tank



Sample illustration

© MEIKO 2016

Technical data

Rack capacity/h (theoretical)	15 / 10 / 7 racks/h
Programme cycle time	240 / 360 / 480 s
Rack dimension	1310 x 690 mm
Entry height	650 mm
Dimensions (W x H x D)	1490 (1600) x 1792 x 995 (1100) mm (with hood rod)
Electrical feeding cable	3-phase current 3 PE 460V 60Hz
	nominal capacity: 4,9 kW
	nominal current: 8,7 A
Protection class of the machine	IP X5
Equipment	MIKE 2 control
	Infrared interface for wireless communication
	Leakage detector
	Soft start
	Wash arm drive
	Boiler safety device
	Drain pump
	Automatic self-cleaning when tank is drained
	Front panel with membrane keypad on the left side
	Main switch, installed
	according to USPH guidelines
	Machine base in marine version
Fresh water line	Air gap 'AA' in accordance with EN 1717 with booster pump
Fresh water supply	Minimum flow pressure 60 kPa / 0,6 bar in front of solenoid valve
	Maximum pressure 500 kPa / 5,0 bar / 72,50 psi
	Max. supply water temperature 140 °F / 60 °C

Technical data sheet



Final rinse water quantity	9,6 liters/cycle / 2,54 U.S.gals/cycle
Steam-heated boiler and tank	Saturated steam, 30 - 200 kPa / 0,3 - 2 bar
	(107,1 - 133,5 °C)
	22,2 kg steam for 15 programme cycles/h
Boiler	Contents: 19,0 I / 5,00 U.S.gals
	Temperature: 85 °C / 185,00 °F
Wash tank	Filling: 100,0 I / 26,42 U.S.gals
	Temperature: 73 °C / 163,40 °F
Wash pump	Performance: 2 x 2,20 kW
Detergent and rinse aid dosage	Preparation for local ECOLAB dosing system, including transformer
Material	Cladding: 1.4301
	Wash tank: 1.4301
	Boiler: 1.4435, 1.4404
Heat emission	for 15 programme cycles/h
	total: 6,7 kW
	perceptible: 4,5 kW
	latent: 2,2 kW
Ventilation flow rate	1710 m³/h / 1006,47 cfm
Steam emission	3,2 kg/h / 7,06 lbs/hr
Emission sound pressure level at the workplace (LpA)	69,5 dB
	419,0 kg / 923,9 lbs

*Note:

Electrical equipment suitable for supply voltage: 3 PE 460 V 60 HZ (3 PE 440-480 V 60 HZ)