Technical data sheet



M-iClean HL

Type: M2

Execution for: Brunei Darussalam

Dishwashing machine

Working direction: right - left Working height: 850 mm

3-phase current: 3N PE 400V 50Hz Fresh water line: Soft cold water 0-3 °dH



Sample illustration

© MEIKO 2018

Technical data

Rack capacity/h (theoretical)	60 / 40 / 17 racks/h
Programme cycle time	60 / 90 / 210 s
Rack dimension	500 x 500 mm to 650 x 500 mm
Entry height	560 mm
Dimensions (W x Hmin x D)	735 (825) x 1575 x 750 (800) mm (with handles)
Electrical feeding cable	3-phase current 3N PE 400V 50Hz*
	nominal capacity: 9,9 kW
	nominal current: 16,3 A
Local fuse protection	20 A
Protection class of the machine	IP X5
Equipment	Control system MIKE CPU4
	Bluetooth interface for wireless communication
	Leakage detector
	Boiler safety device
	Automatic self-cleaning when tank is drained
	Drain pump
	Back wall cladding
	Power Wash
	Automatic hood system
Fresh water line	Air gap 'AB' in accordance with EN 1717 with booster pump
Fresh water supply	Minimum flow pressure 60 kPa / 0,6 bar in front of solenoid valve
	Maximum pressure: 500 kPa / 5,0 bar
	Max. supply water temperature 60 °C
Flow rate	5 l/min

M-iClean page 1 / 2 NN.3.6 M-iPlan 26/04/2024

Technical data sheet



Final rinse water quantity	3,0 liters/cycle, variable
Boiler	Contents: 10,5 I
	Heater: 8,00 kW
	Temperature: 83 °C
	Tank / boiler locked
Wash tank	Filling: 22,0 l
	Heater: 4,00 kW
	Temperature: 60 °C
Wash pump, with frequency converter	Performance: 1,50 kW
Dosing of rinse aid	Hose pump (24 V) with time control
	and suction lance
Detergent dosage	Hose pump (24 V) with time control
-	and suction lance
Material	Cladding: 1.4301
	Wash tank: 1.4301
	Boiler: 1.4571
Heat emission	for 25 programme cycles/h
	total: 2,7 kW
	perceptible: 1,8 kW
	latent: 0,9 kW
Ventilation flow rate	680 m³/h
Steam emission	1,3 kg/h
Emission sound pressure level at the workplace (LpA)	62 / 64 / 67 dB
Net / gross weight	170,0 kg / 210,0 kg (standard packaging)
Packaging dimensions (W x H x D)	1000 x 1800 x 1000 mm (standard packaging)

*Note:

Electrical equipment suitable for supply voltage: 3N PE 400 V 50 HZ (3N PE 380-415 V 50 Hz)

M-iClean page 2 / 2 NN.3.6 M-iPlan 26/04/2024